



Armaturer/säkring

Artikelnr	Beskrivning		B10	B13	B16	C10	C13	C16
	<b>Dimbart 3000 K Borstad</b>	<b>Ø Kupa</b>						
760900-0000	Palla 7609/1900-PE 3K Dim	Ø350	18	25	32	30	41	53
760901-0000	Palla 7609/3200-PE 3K Dim	Ø400	13	18	22	21	30	36
760902-0000	Palla 7609/4500-PE 3K Dim	Ø450	13	18	22	21	30	36
760903-0000	Palla 7609/1800-Glas 3K Dim	Ø350	18	25	32	30	41	53
760904-0000	Palla 7609/3000-Glas 3K Dim	Ø400	13	18	22	21	30	36
760905-0000	Palla 7609/4400-Glas 3K Dim	Ø450	13	18	22	21	30	36
	<b>Dimbart NS6 3000 K Borstad</b>							
760906-0000	Palla 7609/1900-PE 3K Dim NS6	Ø350	18	25	32	30	41	53
760907-0000	Palla 7609/3200-PE 3K Dim NS6	Ø400	13	18	22	21	30	36
760908-0000	Palla 7609/4500-PE 3K Dim NS6	Ø450	13	18	22	21	30	36
760909-0000	Palla 7609/1800-Glas 3K Dim NS6	Ø350	18	25	32	30	41	53
760910-0000	Palla 7609/3000-Glas 3K Dim NS6	Ø400	13	18	22	21	30	36
760911-0000	Palla 7609/4400-Glas 3K Dim NS6	Ø450	13	18	22	21	30	36

	<b>Dimbart 3000 K Vit</b>							
761100-0000	Palla 7611/1900-PE 3K Dim	Ø350	18	25	32	30	41	53
761101-0000	Palla 7611/3200-PE 3K Dim	Ø400	13	18	22	21	30	36
761102-0000	Palla 7611/4500-PE 3K Dim	Ø450	13	18	22	21	30	36
761103-0000	Palla 7611/1800-Glas 3K Dim	Ø350	18	25	32	30	41	53
761104-0000	Palla 7611/3000-Glas 3K Dim	Ø400	13	18	22	21	30	36
761105-0000	Palla 7611/4400-Glas 3K Dim	Ø450	13	18	22	21	30	36
	<b>Dimbart NS6 3000 K Vit</b>							
761106-0000	Palla 7611/1900-PE 3K Dim NS6	Ø350	18	25	32	30	41	53
761107-0000	Palla 7611/3200-PE 3K Dim NS6	Ø400	13	18	22	21	30	36
761108-0000	Palla 7611/4500-PE 3K Dim NS6	Ø450	13	18	22	21	30	36
761109-0000	Palla 7611/1800-Glas 3K Dim NS6	Ø350	18	25	32	30	41	53
761110-0000	Palla 7611/3000-Glas 3K Dim NS6	Ø400	13	18	22	21	30	36
761111-0000	Palla 7611/4400-Glas 3K Dim NS6	Ø450	13	18	22	21	30	36

	<b>Dimbart 3000 K Svart</b>							
761300-0000	Palla 7613/1900-PE 3K Dim	Ø350	18	25	32	30	41	53
761301-0000	Palla 7613/3200-PE 3K Dim	Ø400	13	18	22	21	30	36
761302-0000	Palla 7613/4500-PE 3K Dim	Ø450	13	18	22	21	30	36
761303-0000	Palla 7613/1800-Glas 3K Dim	Ø350	18	25	32	30	41	53
761304-0000	Palla 7613/3000-Glas 3K Dim	Ø400	13	18	22	21	30	36
761305-0000	Palla 7613/4400-Glas 3K Dim	Ø450	13	18	22	21	30	36
	<b>Dimbart NS6 3000 K Svart</b>							
761306-0000	Palla 7613/1900-PE 3K Dim NS6	Ø350	18	25	32	30	41	53
761307-0000	Palla 7613/3200-PE 3K Dim NS6	Ø400	13	18	22	21	30	36
761308-0000	Palla 7613/4500-PE 3K Dim NS6	Ø450	13	18	22	21	30	36
761309-0000	Palla 7613/1800-Glas 3K Dim NS6	Ø350	18	25	32	30	41	53
761310-0000	Palla 7613/3000-Glas 3K Dim NS6	Ø400	13	18	22	21	30	36
761311-0000	Palla 7613/4400-Glas 3K Dim NS6	Ø450	13	18	22	21	30	36

	<b>Dimbart 3000 K Röd</b>							
761500-0000	Palla 7615/1900-PE 3K Dim	Ø350	18	25	32	30	41	53
761501-0000	Palla 7615/3200-PE 3K Dim	Ø400	13	18	22	21	30	36
761502-0000	Palla 7615/4500-PE 3K Dim	Ø450	13	18	22	21	30	36
761503-0000	Palla 7615/1800-Glas 3K Dim	Ø350	18	25	32	30	41	53
761504-0000	Palla 7615/3000-Glas 3K Dim	Ø400	13	18	22	21	30	36
761505-0000	Palla 7615/4400-Glas 3K Dim	Ø450	13	18	22	21	30	36
	<b>Dimbart NS6 3000 K Röd</b>							
761506-0000	Palla 7615/1900-PE 3K Dim NS6	Ø350	18	25	32	30	41	53
761507-0000	Palla 7615/3200-PE 3K Dim NS6	Ø400	13	18	22	21	30	36
761508-0000	Palla 7615/4500-PE 3K Dim NS6	Ø450	13	18	22	21	30	36
761509-0000	Palla 7615/1800-Glas 3K Dim NS6	Ø350	18	25	32	30	41	53
761510-0000	Palla 7615/3000-Glas 3K Dim NS6	Ø400	13	18	22	21	30	36
761511-0000	Palla 7615/4400-Glas 3K Dim NS6	Ø450	13	18	22	21	30	36

	<b>Dimbart 3000 K Grön</b>							
761700-0000	Palla 7617/1900-PE 3K Dim	Ø350	18	25	32	30	41	53
761701-0000	Palla 7617/3200-PE 3K Dim	Ø400	13	18	22	21	30	36
761702-0000	Palla 7617/4500-PE 3K Dim	Ø450	13	18	22	21	30	36
761703-0000	Palla 7617/1800-Glas 3K Dim	Ø350	18	25	32	30	41	53
761704-0000	Palla 7617/3000-Glas 3K Dim	Ø400	13	18	22	21	30	36
761705-0000	Palla 7617/4400-Glas 3K Dim	Ø450	13	18	22	21	30	36
	<b>Dimbart NS6 3000 K Grön</b>							
761706-0000	Palla 7617/1900-PE 3K Dim NS6	Ø350	18	25	32	30	41	53
761707-0000	Palla 7617/3200-PE 3K Dim NS6	Ø400	13	18	22	21	30	36
761708-0000	Palla 7617/4500-PE 3K Dim NS6	Ø450	13	18	22	21	30	36
761709-0000	Palla 7617/1800-Glas 3K Dim NS6	Ø350	18	25	32	30	41	53
761710-0000	Palla 7617/3000-Glas 3K Dim NS6	Ø400	13	18	22	21	30	36
761711-0000	Palla 7617/4400-Glas 3K Dim NS6	Ø450	13	18	22	21	30	36

	<b>Dimbart 3000 K Blå</b>							
761900-0000	Palla 7619/1900-PE 3K Dim	Ø350	18	25	32	30	41	53
761901-0000	Palla 7619/3200-PE 3K Dim	Ø400	13	18	22	21	30	36
761902-0000	Palla 7619/4500-PE 3K Dim	Ø450	13	18	22	21	30	36
761903-0000	Palla 7619/1800-Glas 3K Dim	Ø350	18	25	32	30	41	53
761904-0000	Palla 7619/3000-Glas 3K Dim	Ø400	13	18	22	21	30	36
761905-0000	Palla 7619/4400-Glas 3K Dim	Ø450	13	18	22	21	30	36
	<b>Dimbart NS6 3000 K Blå</b>							
761906-0000	Palla 7619/1900-PE 3K Dim NS6	Ø350	18	25	32	30	41	53
761907-0000	Palla 7619/3200-PE 3K Dim NS6	Ø400	13	18	22	21	30	36
761908-0000	Palla 7619/4500-PE 3K Dim NS6	Ø450	13	18	22	21	30	36
761909-0000	Palla 7619/1800-Glas 3K Dim NS6	Ø350	18	25	32	30	41	53
761910-0000	Palla 7619/3000-Glas 3K Dim NS6	Ø400	13	18	22	21	30	36
761911-0000	Palla 7619/4400-Glas 3K Dim NS6	Ø450	13	18	22	21	30	36

Det här är maxvärden beräknade från startströmmen.

De verkliga värdena kan variera beroende på använda brytartyper och installationsmiljö.

*Information kan ändras utan föregående meddelande.*